
Dual Emitter / Matching Photodector Series

Molded Lead Frame and Leadless Ceramic Substrate

The Dual LED series consists of a 660nm (red) LED and a companion IR LED such as 880/ 895, 905, or 940nm. They are widely used for ratiometeric measurements such as medical analytical and monitoring devices. They can also be used in applications requiring a low cost Bi-Wavelength light source. Two types of pin configurations are available: 1.) three leads with one common anode or cathode, or 2.) two leads parallel back-to-back connection. They are available in two types of packaging. Clear lead frame molded side looker, and leadless ceramic substrate.

The matching photodectors' responses are optimized for maximum responsivity at 660nm as well as near IR wavelengths. They exhibit low capacitance and low dark currents and are available in three different active area sizes in the same two types of packaging as the dual emitters: Clear lead frame molded side looker and leadless ceramic substrate.





APPLICATIONS


- SpO2
- Blood analysis
- Medical Instrumentation
- Ratiometric Instruments

FEATURES

- Leadless ceramic Substrate
- Lead Frame Molded Packages
- Two and Three Lead Designs
- Bi-Wavelengths LEDs
- Matching Detector Response







■ Dual Emitter / Matching Photodector Series

Molded Lead Frame and Leadless Ceramic Substrate

mber	Active Area		Spectral Range	Responsivity		Capacitance	Dark Current (nA)	Max. Reverse Voltage	Operating Temp.	Storage Temp.	
Model Number	Area mm²	Dimensions mm	nm	A/ W		pF	-10 V	V			Package Style
				660nm	900nm	-10V	min.	10μΑ	°C	°C	
Photodiode Characteristics											
PIN-0.81-LLS	0.81	1.02φ	350 - 1100	0.33	0.55	2.0	2	20	-25 ~ +85	-40 ~ +100C	62 / Leadless Cermic
PIN-0.81-CSL											60 / Molded Lead Frame
PIN-4.0-LLS	3.9	2.31 x 1.68				10	5				62 / Leadless Cermic
PIN-4.0-CSL											60 / Molded Lead Frame
PIN-8.0-LLS	8.4	2.9 Sq.				25	10				62 / Leadless Cermic
PIN-8.0-CSL											60 / Molded Lead Frame

For mechanical drawings and pin locations, please refer to pages 58 to 69.

Model Number	LED's Used		Package Style ¶	Pin Configuration	Operating Temperature	Storage Teperature	
Σ	nm				°C	°c	
Dual Emitter Combinations							
DLED-660/880-LLS-2	660	880	64 / Leadless Ceramic	2 Leads / Back to Back*	-25 ~ +85	-40 ~ +80	
DLED-660/895-LLS-2		895					
DLED-660/905-LLS-2		905					
DLED-660/905-LLS-3		905		3 Landa / Camman Anada			
DLED-660/940-LLS-3		940		2 Leads / Common Anode			
DLED-660/880-CSL-2		880	63 / Side Locker Plastic	2 Leads / Back to Back*			
DLED-660/895-CSL-2		895					
DLED-660/905-CSL-2		905					
DLED-660/905-CSL-3		905		214-/			
DLED-660/940-CSL-3		940		3 Leads / Common Anode			

^{*} In Back-to-Back configuration, the LED's are connected in parallel.

	Peak Wavelength	Radiant Flux	Spectral Bandwidth	Forward Voltage	Reverse Voltage				
LED	nm	mW	nm	v	v				
	i _f =20mA	i _f =20mA	i _f =20mA FWHM	i _f =20mA	i _f =20mA				
	typ.	typ.	typ.	max.	max.				
LED Characteristics									
660nm	660	1.8	25	2.4					
880nm	880	1.5	80	2.0	İ				
895nm	895	2.0	50	1.7	5				
905nm	905	=.0							
935nm	935	1.5		1.5					
940nm	940	-10							

For mechanical drawings, please refer to pages 58 thru 69.