

Agilent ADNS-2620 Optical Mouse Sensor Product Overview



#### Description

#### Small Form Factor, Entry-Level Optical Mouse Sensor with Performance Features for Precise Navigation.

The ADNS-2620 is a new entry level, small form factor optical mouse sensor. It is used to implement a non-mechanical tracking engine in computer mice. Unlike its predecessor, this new optical mouse sensor allows for more compact and affordable optical mice designs.

It is based on optical navigation technology which measures changes in position by optically acquiring sequential surface images up to 2300 times per second and mathematically determining the direction and magnitude of movement at the maximum of 400 counts per inch (cpi) and at speeds up to 12 inches per second (ips):

Agilent provides the complete optical mouse sample kit (Part #ADNK-2620). The CMOS based sensor is mounted in an 8-pin staggered dual inline package (DHP) and designed for use with the HDNS-2200 (LED Assembly Clip) and HLMP-ED80-XXXXX (639 nm LED illumination source) and HDNS-2100 (lens). There are no moving parts, so precision optical alignment is not required, thereby facilitating high volume assembly.

#### Theory of Operation

The ADNS-2620 is based on Optical Navigation Technology. It contains an-Image Acquisition System (IAS), a Digital Signal Processor (DSP) and a two wire serial port.

The IAS acquires microscopic surface images via the lens and illumination system provided by the HDNS-2100, HDNS-2200, and HLMP-ED80-XXXXX. These images are processed by the DSP to determine the direction and distance of motion.

# Other available optical mouse sensors from Agilent Technologies:

- ADNS-2030
- ADNS-2051
- HDNS-2000
- ADNS-2610

#### Features

- Precise optical navigation technology
- Small form factor (10 mm x 12.5 mm footprint)
- No mechanical moving parts
- Complete 2D motion sensor
- Common interface for general purpose controller
- Smooth surface navigation
- Programmable frame speed up to 2300 frames per sec (fps)
  - Accurate motion up to 12 ips
- 400 cpi resolution
- High reliability
- High speed motion detector
- Wave solderable
- Single 5.0 volt power supply
- Conforms to USB suspend mode specifications
- Power conservation mode during times of no movement
- Serial port registers
  - Programming
  - Data transfer
- 8-pin staggered dual inline package (DIP)

#### Applications

- Mice for desktop PCs, workstations, and portable PCs
- Trackballs
- Integrated input devices



#### **Navigation by Two Images Comparison**





Figure 1. The Navigation Engine identifies common features in sequential images to determine the direction and amount of mouse movement. Image B was taken while the mouse was moving, a short time after image A.






Figure 3. Circuit-level block diagram for optical mouse solution using an Agilent ADNS-2620 optical mouse sensor.

### ADNS-2620 Specifications

Parameter	Symbol	Min.	Тур.	Max.	Units	Notes
Operating Temperature	T <sub>A</sub>	0		40	°C	
Power Supply Voltage	V <sub>DD</sub>	4.1	5.0	5.5	V	Register values retained for voltage transients below 4.10V but greater than 3.9V.
DC Supply Current (mouse moving)	I <sub>DD AVG</sub>		15	30	mA	
DC Supply Current (mouse not moving)	I <sub>DD</sub>		12		mA	
DC Supply Current (power down)	I <sub>DDPD</sub>		170	230	μΑ	
Clock Frequency	f <sub>CLK</sub>	23.0	24.0	25.0	MHz	Set by ceramic resonator
Resonator Impedance	X <sub>RES</sub>			55	Ω	
Distance from lens reference plane to surface	Z	2.3	2.4	2.5	mm	Results in ±0.2mm/DOF
Speed	S	0		12	in/sec	@ frame rate = 1500 fps
Acceleration	А			0.25	g 🔿	@ frame rate = 1500 fps
Light level onto IC	IRR <sub>INC</sub>	80 100		25,000 30,000	mW/m²	λ = 639 nm λ = 875 nm
Resolution	RES		400	$\frown$	counts/in	$\vee/$
Frame Rate	FR		1500	2300	frames/s	

 $\bigcirc$ 

3

## www.agilent.com/semiconductors

 $\langle \rangle$ 

distributors, please go to our web site For technical assistance call: Americas/Canada: +1 (800) 235-0312 or (916) 788-6763 Europe: +49 (0) 6441 92460 China: 10800 650 0017 Hong Kong: (65) 6756 2394

India, Australia, New Zeatand: (45) (6755 1939 Japan: (+81 3) 3325-8152(Oppestic:/International), or 0120-61-1280(Domestic:Only)

Korea: (65) 6755 1989

Singapore, Malaysia, Vietnam, Thailand, Philippines, Indonesia: (65) 6755 2044

Taiwan: (65) 6755 1843

Data subject to change. Copyright © 2003 Agilent Technologies, Inc. Obsoletes 5988-9166EN June 17, 2003 5988-9775EN

